



KR15P

DIN rail terminal 35-150mm², gray

Technical properties

Architecture

| | |
|-------------|--|
| Fixing mode | on mounting rail according to DIN EN 50022 |
|-------------|--|

Main electrical features

| | |
|--|--------|
| Rated operational voltage U _e | 1000 V |
|--|--------|

Electric current

| | |
|---------------|-------|
| Rated current | 309 A |
|---------------|-------|

Dimensions

| | |
|-----------------------------|----------|
| Depth of installed product | 100 mm |
| Height of installed product | 118.5 mm |
| Width of installed product | 31 mm |

Materials

| | |
|----------|---------------|
| Colour | stone grey |
| Colour | dark grey |
| Material | Polyamid (PA) |

Connection

| | |
|---|--------------------------|
| Connection cross section (solid-core) | 35 ; 150 mm ² |
| Connection cross section (fine-strand) | 50 ; 150 mm ² |
| Connection cross-sect. flexible conductor | 35 / 150mm ² |
| Connection cross-sect. rigid cable | 35 / 150mm ² |
| Conductor cross-section (flexible), with wire end sleeve | 50...150 mm ² |
| Conductor cross-section (flexible), without wire end sleeve | 50...150 mm ² |
| Type of connection | with screw |

Settings

| | |
|---------------|------------------|
| terminal type | In-line terminal |
|---------------|------------------|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Use conditions

| | |
|-----------------------|--------------|
| Operating temperature | -60...105 °C |
|-----------------------|--------------|