



Insulated busbar 3P+N 63A prong 10mm² 48C for MCB 1P+N 1 module

Technical properties

Architecture

Number of poles	4 P
Type of pole	3P+N

Configuration

Number of modules	24
-------------------	----

Compatibility

Intended for the compatible references	MCB 1P+N
--	----------

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	63 A
---------------	------

Dimensions

Length	428 mm
Pitch	17.8 mm

Power supply

Number of phases for the power supply	3 phases
---------------------------------------	----------

Materials

Colour	stone grey
--------	------------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Connection cross-sect. rigid cable	10mm ²
Suitable for product with neutral busbar	Yes
Connector type	busbar prong
Type of connection	with screw

Equipment

Number of appliances to build in	6
----------------------------------	---

KBN663C

Standards

European directive WEEE

concerned

Use conditions

Insulated

Yes