



**Insulated busbar3P+N 63A prong 10mm<sup>2</sup> 48C for MCB 1P+N 1 module**

**Technical properties**

**Architecture**

Number of poles 4 P

**Configuration**

Number of modules 24

**Compatibility**

Intended for the compatible references MCB 1P+N

**Main electrical features**

Rated operational voltage Ue 230 / 400 V

**Voltage**

Max operating voltage 400 V

Rated impulse withstand voltage 4 kV

**Electric current**

Rated current 63 A

**Dimensions**

Length 428 mm

Pitch 17.8 mm

**Power supply**

Number of phases for the power supply 3 phases

**Installation, mounting**

Suitable to a device with an auxiliary No

**Connection**

Connection cross-sect. rigid cable 10mm<sup>2</sup>

Suitable for product with neutral busbar Yes

Connector type busbar prong

**Equipment**

Number of appliances to build in 6

**Standards**

European directive WEEE concerned

**Use conditions**

Insulated Yes

KBN663C