



LB113



Fuse carrier 1P 5A 240V BS1361 1M with cartridge fuse

Technical properties

Architecture

Type of pole	1 P
--------------	-----

Configuration

Number of modules	1
-------------------	---

Controls and indicators

Indicator lamp	no
----------------	----

Connectivity

Top connection alignment for modular devices	Aligned terminal
--	------------------

Main electrical features

Rated operational voltage Ue	240 V
------------------------------	-------

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	5 A
---------------	-----

Rating current of fuse cartridge	5 A
----------------------------------	-----

Fuse

CharactFuse	BS1361
-------------	--------

Fuse Size	6.3 x 23
-----------	----------

Power

Power loss per pole at In	0.02 W
---------------------------	--------

Endurance

Electric endurance in number of cycles	2000
--	------

Number of mechanical operations	4000
---------------------------------	------

Installation, mounting

Tightening torque	2,2Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	0,75 / 16mm ²
---	--------------------------

Connection cross-sect. rigid cable	1 / 25mm ²
------------------------------------	-----------------------

Use conditions

Operating temperature	-5...50 °C
-----------------------	------------

Degree of pollution according to IEC 60664 / IEC 60947-2	3
--	---

Storage/transport temperature

-25...80 °C

temperatur

Temperature of calibration

30 °C