



KDN163A

**Insulated busbar 1P 63A fork 10mm<sup>2</sup> 12M**

**Technical properties**

**Architecture**

|                 |     |
|-----------------|-----|
| Number of poles | 1 P |
| Type of pole    | 1 P |

**Compatibility**

|  |                 |
|--|-----------------|
| Intended for the compatible references | Modular devices |
|--|-----------------|

**Main electrical features**

|                              |       |
|------------------------------|-------|
| Rated operational voltage Ue | 415 V |
|------------------------------|-------|

**Voltage**

|                       |       |
|-----------------------|-------|
| Max operating voltage | 230 V |
|-----------------------|-------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

**Dimensions**

|        |         |
|--------|---------|
| Length | 210 mm  |
| Pitch  | 17.8 mm |

**Materials**

|        |            |
|--------|------------|
| Colour | stone grey |
|--------|------------|

**Installation, mounting**

|  |    |
|--|----|
| Suitable to a device with an auxiliary | No |
|--|----|

**Connection**

|  |    |
|--|----|
| Suitable for product with neutral busbar | No |
|--|----|

**Equipment**

|                                  |    |
|----------------------------------|----|
| Number of appliances to build in | 12 |
|----------------------------------|----|

**Standards**

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | No  |
| RoHS conform  | Yes |

**Use conditions**

|           |     |
|-----------|-----|
| Insulated | Yes |
|-----------|-----|