



KJ02C

Distribution block,160A,1pole,1x 10-70²/6x 2,5-16²/1x flat copper 16x5 lateral

Technical properties

Architecture

| | |
|-----------------|-----|
| Number of poles | 1 P |
|-----------------|-----|

Configuration

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Electric current

| | |
|---------------|-------|
| Rated current | 160 A |
|---------------|-------|

Dimensions

| | |
|----------------------------|-------|
| Depth of installed product | 50 mm |
|----------------------------|-------|

| | |
|-----------------------------|-------|
| Height of installed product | 90 mm |
|-----------------------------|-------|

| | |
|----------------------------|-------|
| Width of installed product | 35 mm |
|----------------------------|-------|

Materials

| | |
|----------|-------|
| Material | brass |
|----------|-------|

Connection

| | |
|--|-------------------------|
| Conductor cross-section (flexible), with wire end sleeve | 10...50 mm ² |
|--|-------------------------|

| | |
|---------------------------------|-------------------------|
| Conductor cross-section (rigid) | 10...70 mm ² |
|---------------------------------|-------------------------|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------|----|
| REACH conform | No |
|---------------|----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

| | |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|