



LS612



**Fuse carrier 1P+N 50A 690V L51 accessoriability 3M**

**Technical properties**

**Architecture**

|                 |      |
|-----------------|------|
| Number of poles | 2 P  |
| Type of pole    | 1P+N |

**Configuration**

|                   |   |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 50 A |
|---------------|------|

**Fuse**

|             |         |
|-------------|---------|
| CharactFuse | gG ; aM |
|-------------|---------|

**Dimensions**

|                             |         |
|-----------------------------|---------|
| Depth of installed product  | 93 mm   |
| Height of installed product | 107 mm  |
| Width of installed product  | 52.5 mm |

**Power**

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 8.3 W |
|---------------------------|-------|

**Standards**

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

**Safety**

|                     |      |
|---------------------|------|
| Protection index IP | IP20 |
| REACH conform       | Yes  |
| RoHS conform        | Yes  |

**Use conditions**

|  |             |
|--|-------------|
| Operating temperature                                    | -5...40 °C  |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3           |
| Storage/transport temperature                            | -25...80 °C |