



LS670

Microswitch 1P for fuse carrier L51

Technical properties

Architecture

Number of poles 1 P

Configuration

Number of modules 0.5

Compatibility

Suitable for Fuse carrier

Main electrical features

Rated operational voltage Ue 220 / 250 V

Frequency 40/60 Hz

Voltage

Rated insulation voltage 6000 V

Rated operational voltage in DC 24 V

Electric current

Acceptable current rating with AC1 5 A

I_{min} = f (U = 230 V AC) 5 A

Fuse

Fuse Size 14 x 51

Dimensions

Depth of installed product 20 mm

Height of installed product 35 mm

Width of installed product 35 mm

Connection

Type of connection fast-on terminal

Equipment

Quantity of NC contacts 0

Quantity of NO contacts 0

Quantity of INV contacts 1

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature	-5...40 °C
Air humidity protection	95% / 80°C
Storage/transport temperature	-25...55 °C
