



LS770

Microswitch 1P for fuse carrier L58

Technical properties

Architecture

Number of poles	1 P
-----------------	-----

Compatibility

Suitable for	Fuse carrier
--------------	--------------

Main electrical features

Rated operational voltage U _e	220 / 250 V
--	-------------

Frequency	40/60 Hz
-----------	----------

Voltage

Rated insulation voltage	6000 V
--------------------------	--------

Rated operational voltage in DC	24 / 220 V
---------------------------------	------------

Electric current

Acceptable current rating with AC1	5 A
------------------------------------	-----

I _{min} = f (U = 230 V AC)	5 A
-------------------------------------	-----

Fuse

Fuse Size	22 x 58
-----------	---------

Dimensions

Depth of installed product	20 mm
----------------------------	-------

Height of installed product	35 mm
-----------------------------	-------

Width of installed product	35 mm
----------------------------	-------

Connection

Type of connection	fast-on terminal
--------------------	------------------

Equipment

Quantity of NC contacts	0
-------------------------	---

Quantity of NO contacts	0
-------------------------	---

Quantity of INV contacts	1
--------------------------	---

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Use conditions

Operating temperature	-5...40 °C
-----------------------	------------

Air humidity protection

95% / 80°C

Storage/transport temperature

-25...55 °C