



LF402M

Industrial fuse-links 14x51 aM 2A

Technical properties

Functions

| | |
|------------------------------|----------|
| Release characteristic fuses | Time-lag |
|------------------------------|----------|

Main electrical features

| | |
|--|-------|
| Rated short circuit breaking capacity I_{cn} AC according IEC60898-1 | 80 kA |
| Rated operational voltage U_e | 690 V |
| Type of supply voltage | AC |

Electric current

| | |
|--|-------|
| Rated current | 2 A |
| Rated ultimate short-circuit breaking capacity I_{cu} AC IEC 60947-2 | 80 kA |

Fuse

| | |
|-------------|---------|
| CharactFuse | gG ; aM |
| Fuse Size | 14 x 51 |

Frequency

| | |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

Power

| | |
|------------------------------|--------|
| Total power loss under I_N | 0.24 W |
|------------------------------|--------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |