



LS502



**Fuse carrier 2P 32A 690V L38 2M**

**Technical properties**

**Architecture**

|                 |     |
|-----------------|-----|
| Number of poles | 2 P |
| Type of pole    | 2 P |

**Configuration**

|                   |   |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

**Main electrical features**

|                        |    |
|------------------------|----|
| Type of supply voltage | AC |
|------------------------|----|

**Voltage**

|                          |       |
|--------------------------|-------|
| Rated insulation voltage | 690 V |
|--------------------------|-------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 32 A |
|---------------|------|

**Dimensions**

|                             |       |
|-----------------------------|-------|
| Depth of installed product  | 75 mm |
| Height of installed product | 83 mm |
| Width of installed product  | 36 mm |

**Frequency**

|           |             |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

**Power**

|                           |       |
|---------------------------|-------|
| Total power loss under IN | 7.4 W |
|---------------------------|-------|

**Installation, mounting**

|                   |       |
|-------------------|-------|
| Tightening torque | 2,2Nm |
|-------------------|-------|

**Equipment**

|                     |     |
|---------------------|-----|
| Can be accessorized | Yes |
|---------------------|-----|

**Standards**

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

**Safety**

|                     |      |
|---------------------|------|
| Protection index IP | IP20 |
| REACH conform       | Yes  |
| RoHS conform        | Yes  |

**Use conditions**

|   |             |
|---|-------------|
| Operating temperature                                       | -5...50 °C  |
| Degree of pollution according to IEC 60664 /<br>IEC 60947-2 | 3           |
| Storage/transport temperature                               | -25...80 °C |