



MM513N



## Motor protection circuit breaker 3P 20-25A ; 5.5/12.5 kW at 230/415V

### Technical properties

#### Architecture

Type of order	Short thumb-grip
Number of poles	3 P
Type of pole	3 P

#### Configuration

Number of modules	2.5
-------------------	-----

#### Main electrical features

Rated operational voltage Ue	690 V
Type of supply voltage	AC
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	6000 V

#### Electric current

Rated current	25 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	3 kA
Magnetic regulating current	12.4 / 15.5 / 18.6 In
Thermal trip setting with 30°	20 / 20.6 / 21.3 / 21.9 / 22.5 / 23.1 / 23.8 / 24.4 / 25 A
Rating current 0°C according to IEC 60947	25 A
Rating current 10°C according to IEC 60947	25 A
Rating current 20°C according to IEC 60947	25 A
Rating current 30°C according to IEC 60947	25 A
Rating current 40°C according to IEC 60947	25 A
Rating current 50°C according to IEC 60947	25 A
Rated service breaking capacity Ics AC according IEC 60947-2	75 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	50 kA

**Dimensions**

Strip length of main circuit connections	10 mm
--	-------

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Total power loss under IN	5.82 W
---------------------------	--------

Standard power rating of 3 phase motor in AC3 under 230V	5.5 kW
--	--------

Standard power rating of 3 phase motor in AC3 under 400V	12.5 kW
--	---------

Rated operational power for 3P under 220-230V AC3 according IEC60947-4	5.5 kW
--	--------

Rated operational power for 3P under 240V AC3 according IEC60947-4	5.5 kW
--	--------

Rated operational power for 3P under 415V AC3 according IEC60947-4	12.5 kW
--	---------

Rated operational power for 3P under 440V AC3 according IEC60947-4	12.5 kW
--	---------

Rated operational power for 3P under 500V AC3 according IEC60947-4	15 kW
--	-------

**Electrical specifications**

Nominal tightening torque of main circuit	1.7 Nm
---	--------

**Endurance**

Electric endurance in number of cycles	50000
--	-------

Mechanical endurance in number of operations per hour	40
---	----

Number of mechanical operations	100000
---------------------------------	--------

**Installation, mounting**

Tightening torque	1,7Nm
-------------------	-------

Type connection of power circuit	with screw
----------------------------------	------------

**Connection**

Connection cross-section of input and output with screws, for massive conductors	1 / 6 mm <sup>2</sup>
--	-----------------------

Connection cross section of access and exit with screws, for flexible conductor	1 / 6 mm <sup>2</sup>
---	-----------------------

Cable flexibel cross section for main circuit	1x (1 - 6) mm <sup>2</sup> / 2x (1 - 6) mm <sup>2</sup>
---	---

Cable rigid cross section for main circuit	1x (1 - 6) mm <sup>2</sup> / 2x (1 - 6) mm <sup>2</sup>
--	---

Type of connection	with screw
--------------------	------------

**Settings**

min/maxi threshold value of the AC magnetic operation	310 / 465 A
---	-------------

Setting type In or Ith	IN
------------------------	----

**Equipment**

Automatic compensation of the temperature	-5 / 40 °C
---	------------

Can be accessorized	Yes
---------------------	-----

**Use cases**

**Standards**

Standard text	IEC 60947-4-1 ; EN 60947-4-1
European directive RoHs	voluntary compliance

**Safety**

REACH conform	Yes
RoHS conform	Yes
Phase failure sensitive	Yes

**Use conditions**

Operating temperature	-25...55 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C

**temperatur**

Temperature of calibration	30 °C
----------------------------	-------