



LS503



Fuse carrier 3P 32A 690V L38 3M

Technical properties

Architecture

| | |
|-----------------|-----|
| Number of poles | 3 P |
| Type of pole | 3 P |

Configuration

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Main electrical features

| | |
|------------------------|----|
| Type of supply voltage | AC |
|------------------------|----|

Voltage

| | |
|--------------------------|-------|
| Rated insulation voltage | 690 V |
|--------------------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 32 A |
|---------------|------|

Fuse

| | |
|-------------|-----------|
| CharactFuse | gG ; aM |
| Fuse Size | 10.3 x 38 |

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 75 mm |
| Height of installed product | 83 mm |
| Width of installed product | 54 mm |

Frequency

| | |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

Power

| | |
|---------------------------|--------|
| Total power loss under IN | 11.1 W |
|---------------------------|--------|

Installation, mounting

| | |
|-------------------|-------|
| Tightening torque | 2,2Nm |
|-------------------|-------|

Equipment

| | |
|---------------------|-----|
| Can be accessorized | Yes |
|---------------------|-----|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |

Use conditions

| | |
|---|-------------|
| Operating temperature | -5...50 °C |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
| Storage/transport temperature | -25...80 °C |