



LS604



Fuse carrier 3P+N 50A 690V L51 accessoriability 6M

Technical properties

Architecture

| | |
|-----------------|------|
| Number of poles | 4 P |
| Type of pole | 3P+N |

Configuration

| | |
|-------------------|---|
| Number of modules | 6 |
|-------------------|---|

Electric current

| | |
|---------------|------|
| Rated current | 50 A |
|---------------|------|

Fuse

| | |
|-------------|---------|
| CharactFuse | gG ; aM |
|-------------|---------|

Dimensions

| | |
|-----------------------------|--------|
| Depth of installed product | 93 mm |
| Height of installed product | 107 mm |
| Width of installed product | 105 mm |

Power

| | |
|---------------------------|---------|
| Total power loss under IN | 20.16 W |
|---------------------------|---------|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
| REACH conform | Yes |
| RoHS conform | Yes |

Use conditions

| | |
|----------------------------------------------------------|-------------|
| Operating temperature | -5...40 °C |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
| Storage/transport temperature | -25...80 °C |