



LS712



Fuse carrier 1P+N 125A 690V L58 accessoriability 4M

Technical properties

Architecture

Number of poles	2 P
Type of pole	1P+N

Configuration

Number of modules	4
-------------------	---

Electric current

Rated current	125 A
---------------	-------

Dimensions

Depth of installed product	96 mm
Height of installed product	125 mm
Width of installed product	70 mm

Power

Total power loss under IN	17.6 W
---------------------------	--------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-5...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C