



LS771

Microswitch 3P for fuse carrier L58

Technical properties

Architecture

Number of poles	3 P
-----------------	-----

Configuration

Number of modules	0.5
-------------------	-----

Compatibility

Suitable for	Fuse carrier
--------------	--------------

Main electrical features

Rated operational voltage Ue	220 / 250 V
------------------------------	-------------

Voltage

Rated insulation voltage	6000 V
--------------------------	--------

Rated operational voltage in DC	24 / 220 V
---------------------------------	------------

Electric current

Acceptable current rating with AC1	5 A
------------------------------------	-----

I _{min} = f (U = 230 V AC)	5 A
-------------------------------------	-----

Dimensions

Width of installed product	9 mm
----------------------------	------

Equipment

Quantity of NC contacts	0
-------------------------	---

Quantity of NO contacts	0
-------------------------	---

Quantity of INV contacts	1
--------------------------	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Use conditions

Operating temperature	-5...40 °C
-----------------------	------------

Storage/transport temperature	-25...55 °C
-------------------------------	-------------