



MM505N



**Motor protection circuit breaker 3P 0.63-1A ; 0.12/0.25 kW at 230/415V**

**Technical properties**

**Architecture**

Type of order	Short thumb-grip
Number of poles	3 P
Type of pole	3 P

**Configuration**

Number of modules	2.5
-------------------	-----

**Main electrical features**

Rated operational voltage Ue	690 V
Type of supply voltage	AC
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	690 V
Rated impulse withstand voltage	6000 V

**Electric current**

Rated current	1 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	150 kA
Magnetic regulating current	12.4 / 15.5 / 18.6 In
Thermal trip setting with 30°	0.63 / 0.68 / 0.72 / 0.77 / 0.82 / 0.86 / 0.91 / 0.95 / 1 A
Rating current 0°C according to IEC 60947	0.04 A
Rating current 10°C according to IEC 60947	0.04 A
Rating current 20°C according to IEC 60947	0.04 A
Rating current 30°C according to IEC 60947	0.04 A
Rating current 40°C according to IEC 60947	0.04 A
Rating current 50°C according to IEC 60947	0.04 A
Rated service breaking capacity Ics AC according IEC 60947-2	100 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	150 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	150 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	150 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	150 kA

Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	150 kA
--	--------

### Dimensions

Strip length of main circuit connections	10 mm
--	-------

### Frequency

Frequency	50 to 60 Hz
-----------	-------------

### Power

Total power loss under IN	5.33 W
Standard power rating of 3 phase motor in AC3 under 230V	0.12 kW
Standard power rating of 3 phase motor in AC3 under 400V	0.25 kW
Rated operational power for 3P under 220-230V AC3 according IEC60947-4	0.12 kW
Rated operational power for 3P under 240V AC3 according IEC60947-4	0.12 kW
Rated operational power for 3P under 415V AC3 according IEC60947-4	0.25 kW
Rated operational power for 3P under 440V AC3 according IEC60947-4	0.25 kW
Rated operational power for 3P under 500V AC3 according IEC60947-4	0.38 kW

### Electrical specifications

Nominal tightening torque of main circuit	1.7 Nm
---	--------

### Endurance

Electric endurance in number of cycles	50000
Mechanical endurance in number of operations per hour	40
Number of mechanical operations	100000

### Installation, mounting

Tightening torque	1,7Nm
Type connection of power circuit	with screw

### Connection

Connection cross-section of input and output with screws, for massive conductors	1 / 6 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	1 / 6 mm <sup>2</sup>
Cable flexibel cross section for main circuit	1x (1 - 6) mm <sup>2</sup> / 2x (1 - 6) mm <sup>2</sup>
Cable rigid cross section for main circuit	1x (1 - 6) mm <sup>2</sup> / 2x (1 - 6) mm <sup>2</sup>
Type of connection	with screw

### Settings

min/maxi threshold value of the AC magnetic operation	12.4 / 18.6 A
Setting type In or Ith	IN

### Equipment

Automatic compensation of the temperature	-5 / 40 °C
---	------------

Can be accessorized	Yes
---------------------	-----

---

**Use cases**

Category of use	AC3
-----------------	-----

---

**Standards**

Standard text	IEC 60947-4-1 ; EN 60947-4-1
---------------	------------------------------

European directive RoHs	voluntary compliance
-------------------------	----------------------

---

**Safety**

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Phase failure sensitive	Yes
-------------------------	-----

---

**Use conditions**

Operating temperature	-25...55 °C
-----------------------	-------------

Degree of pollution according to IEC 60664 / IEC 60947-2	3
---	---

Storage/transport temperature	-25...80 °C
-------------------------------	-------------

---

**temperatur**

Temperature of calibration	30 °C
----------------------------	-------