



MZ527N



Alarm contact for motor starter 2C

Technical properties

Architecture

Maximum poles of the main device	3
----------------------------------	---

Configuration

Number of modules	0.5
-------------------	-----

Main electrical features

Rated operational voltage U _e	220 / 500 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	6000 V
Rated operational voltage in DC	24 / 220 V

Electric current

Acceptable current rating with AC1	3 A
Simulation fault current	No
Maximum current	25 A
Rated current	1 A
I _{min} = f (U = 230 V AC)	3 A
I _{min} = f (U = 230 V DC)	0.25 A
I _{min} =f(U=400V AC) for power circuit	2 A
I _{min} =f(U=24V DC) for power circuit	2 A

Dimensions

Depth of installed product	68 mm
Width of installed product	9 mm

Power

Total power loss under I _N	0.2 W
Power loss per pole at I _N	0.1 W

Endurance

Electric endurance in number of cycles	5000
Number of mechanical operations	10000

Installation, mounting

Factory fitted	No
----------------	----

Connection

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	2
Number of auxiliary contacts as change-over contact	0
Quantity of NC contacts	0
Quantity of NO contacts	2
Quantity of INV contacts	0
Number of auxiliary contacts as fault signal	2

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...55 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Storage/transport temperature	-25...80 °C