



MZ903

Remote control auxiliary

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Main electrical features

| | |
|------------------------------|-------------------|
| Rated operational voltage Ue | 207 / 230 / 253 V |
| Type of supply voltage | AC |
| Frequency | 50/60 Hz |

Voltage

| | |
|---------------------------------|-------------------|
| Rated insulation voltage | 6 kV |
| Command voltage AC | 207 / 230 / 253 V |
| Rated operational voltage in DC | 230 V |

Electric current

| | |
|------------------------------------|------|
| Acceptable current rating with AC1 | 5 A |
| Quiescent current | 0 mA |

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 71 mm |
| Height of installed product | 83 mm |
| Width of installed product | 54 mm |

Power

| | |
|---------------------------|---------|
| Inrush power absorbed | 1173 VA |
| Total power loss under IN | 0.11 W |

Equipment

| | |
|--------------------------|---|
| Quantity of NC contacts | 0 |
| Quantity of NO contacts | 2 |
| Quantity of INV contacts | 0 |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---|-----|
| Dielectric properties distance between coil and contact | 6Kv |
|---|-----|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...40 °C |
|-----------------------|------------|