



MZ903

#### Remote control auxiliary

#### Technical properties

##### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

##### Main electrical features

|                              |                   |
|------------------------------|-------------------|
| Rated operational voltage Ue | 207 / 230 / 253 V |
| Type of supply voltage       | AC                |
| Frequency                    | 50/60 Hz          |

##### Voltage

|                                 |                   |
|---------------------------------|-------------------|
| Rated insulation voltage        | 6 kV              |
| Command voltage AC              | 207 / 230 / 253 V |
| Rated operational voltage in DC | 230 V             |

##### Electric current

|                                    |      |
|------------------------------------|------|
| Acceptable current rating with AC1 | 5 A  |
| Quiescent current                  | 0 mA |

##### Dimensions

|                             |       |
|-----------------------------|-------|
| Depth of installed product  | 71 mm |
| Height of installed product | 83 mm |
| Width of installed product  | 54 mm |

##### Power

|                           |         |
|---------------------------|---------|
| Inrush power absorbed     | 1173 VA |
| Total power loss under IN | 0.11 W  |

##### Equipment

|                          |   |
|--------------------------|---|
| Quantity of NC contacts  | 0 |
| Quantity of NO contacts  | 2 |
| Quantity of INV contacts | 0 |

##### Standards

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

##### Safety

|   |     |
|---|-----|
| Dielectric properties distance between coil and contact | 6Kv |
|---|-----|

##### Use conditions

|                       |            |
|-----------------------|------------|
| Operating temperature | -5...40 °C |
|-----------------------|------------|