



MZ901

Remote control auxiliary

Technical properties

Configuration

Number of modules	3
-------------------	---

Main electrical features

Rated operational voltage Ue	207 / 230 / 253 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	6 kV
Command voltage AC	207 / 230 / 253 V
Rated operational voltage in DC	230 V

Electric current

Acceptable current rating with AC1	5 A
Quiescent current	0 mA

Dimensions

Depth of installed product	71 mm
Height of installed product	83 mm
Width of installed product	54 mm

Power

Inrush power absorbed	1173 VA
Total power loss under IN	0.11 W

Installation, mounting

Tightening torque	1,7Nm;0,6Nm
-------------------	-------------

Connection

Connection cross-sect. flexible conductor	terminals 1 and 3 : 1 to 6mm ² / terminals 2 up to 18 : 0,2 to 2,5mm ²
Connection cross-sect. rigid cable	Terminals 1 and 2 : 1,5 / 10mm ² - Terminals 2 up to 8 : 0,2 / 2,5mm ²

Equipment

Quantity of NC contacts	0
Quantity of NO contacts	2
Quantity of INV contacts	0

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Dielectric properties distance between coil
and contact

6Kv

Use conditions

Operating temperature

-5...40 °C