



NF363A

**MCB 3P 6/10kA C-63A 3M**

**Technical properties**

**Architecture**

Number of protected poles	3
Number of poles	3 P
Type of pole	3 P
Curve	C

**Functions**

Concurrently switching N-neutral	No
----------------------------------	----

**Configuration**

Number of modules	3
-------------------	---

**Connectivity**

Top connection alignment for modular devices	Aligned terminal
Bottom connection alignment for modular devices	Aligned terminal

**Main electrical features**

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	6 kA
Rated operational voltage $U_e$	230 / 400 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated current	63 A
Rated service breaking capacity $I_{cs}$ AC according IEC 60898-1	6 kA
min/maxi threshold value of the AC thermal operation	1.13 / 1.45 $I_n$
Magnetic regulating current	5 / 10 $I_n$
min/maxi threshold value of the DC magnetic operation	7 / 15 $I_n$
min/maxi threshold value of the DC thermal operation	1.13 / 1.45 $I_n$
Breaking capacity on 1 pole for IT 400V NF 60947-2	3 kA
Rated short circuit breaking capacity $I_{cn}$ under 400V AC according IEC60898-1	6 kA

Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	10 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	10 kA
<b>Electric current / temperature</b>	
Rating current -25°C	78.9 A
Rating current -20°C	77.6 A
Rating current -15°C	76.2 A
Rating current -10°C	74.9 A
Rating current -5°C	73.5 A
Rating current 0°C	72.1 A
Rating current 5°C	70.7 A
Rating current 10°C	69.2 A
Rating current 15°C	67.7 A
Rating current 20°C	66.2 A
Rating current 25°C	64.6 A
Rating current 30°C	63 A
Rating current 35°C	61.4 A
Rating current 40°C	59.7 A
Rating current 45°C	57.9 A
Rating current 50°C	56.1 A
Rating current 55°C	54.3 A
Rating current 60°C	52.4 A
Rating current 65°C	50.7 A
Rating current 70°C	48.9 A
<b>Current correction factors</b>	
Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.95
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.9
Correction factor of rating current for 6 devices placed side-by-side	0.85
Correction factor of magnetic tripping with 100 Hz	1.1
Correction factor of magnetic tripping with 200 Hz	1.2
Correction factor of magnetic tripping with 400 Hz	1.5
Correction factor of magnetic tripping with 60 Hz	1
<b>Dimensions</b>	
Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	52.5 mm
<b>Frequency</b>	
Frequency	50 to 60 Hz

<b>Power</b>	
Total power loss under IN	18.1 W
Power loss per pole at In	6.24 W
<b>Endurance</b>	
Electric endurance in number of cycles	4000
Number of mechanical operations	20000
<b>Installation, mounting</b>	
Type of top connection for modular devices	with screw
Tightening torque	2,8Nm
Type of top rail clip for modular devices	NA
Type of bottom rail clip for modular devices	metallic
Type of Bottom Connection for modular devices	Blconnect
Top removability for modular devices	No
Bottom removability for modular devices	No
<b>Connection</b>	
Connection cross-section of input and output with screws, for massive conductors	1 / 35 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	1 / 25 mm <sup>2</sup>
Type of connection	with screw
<b>Standards</b>	
Standard text	EN 60898-1
European directive WEEE	not concerned
<b>Safety</b>	
REACH conform	No
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Operating temperature	-25...70 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-25...80 °C
<b>Identification</b>	
Aesthetic for B.G. Protection devices	FD