



NRN325



MCB 3P 25kA C-25A 3M

Technical properties

Architecture

| | |
|---------------------------|-----------------|
| Neutral position | without neutral |
| Number of protected poles | 3 |
| Number of poles | 3 P |
| Type of pole | 3 P |
| Curve | C |

Functions

| | |
|----------------------------------|----|
| Concurrently switching N-neutral | No |
|----------------------------------|----|

Configuration

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Connectivity

| | |
|---|------------------|
| Top connection alignment for modular devices | Aligned terminal |
| Bottom connection alignment for modular devices | Aligned terminal |

Main electrical features

| | |
|--|-------|
| Rated short circuit breaking capacity I_{cn} AC according IEC60898-1 | 10 kA |
| Rated operational voltage U_e | 415 V |
| Type of supply voltage | AC |

Voltage

| | |
|---------------------------------|--------|
| Rated insulation voltage | 500 V |
| Max operating voltage | 415 V |
| Rated impulse withstand voltage | 6000 V |

Electric current

| | |
|---|-------------------|
| Rated current | 25 A |
| Rated service breaking capacity I_{cs} AC according IEC 60898-1 | 7.5 kA |
| min/maxi threshold value of the AC thermal operation | 1.13 / 1.45 I_n |
| Magnetic regulating current | 5 / 10 I_n |
| min/maxi threshold value of the DC magnetic operation | 5 / 15 I_n |
| min/maxi threshold value of the DC thermal operation | 1.13 / 1.45 I_n |
| Rating current -10°C according to IEC 60947 | 35.44 A |

| | |
|---|---------|
| Rating current -15°C according to IEC 60947 | 35.87 A |
| Rating current -20°C according to IEC 60947 | 36.3 A |
| Rating current -25°C according to IEC 60947 | 36.73 A |
| Rating current -5°C according to IEC 60947 | 35.01 A |
| Rating current 0°C according to IEC 60947 | 34.58 A |
| Rating current 10°C according to IEC 60947 | 33.72 A |
| Rating current 15°C according to IEC 60947 | 33.29 A |
| Rating current 20°C according to IEC 60947 | 32.86 A |
| Rating current 25°C according to IEC 60947 | 32.43 A |
| Rating current 30°C according to IEC 60947 | 32 A |
| Rating current 35°C according to IEC 60947 | 30.25 A |
| Rating current 40°C according to IEC 60947 | 28.5 A |
| Rating current 45°C according to IEC 60947 | 26.75 A |
| Rating current 5°C according to IEC 60947 | 34.15 A |
| Rating current 50°C according to IEC 60947 | 25 A |
| Rating current 55°C according to IEC 60947 | 23.25 A |
| Rating current 60°C according to IEC 60947 | 21.5 A |
| Rating current 65°C according to IEC 60947 | 19.75 A |
| Rating current 70°C according to IEC 60947 | 18 A |
| Breaking capacity on 1 pole for IT 400V NF 60947-2 | 3 kA |
| Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1 | 10 kA |
| Rated short circuit breaking capacity Icn under 400V AC according IEC60898-1 | 10 kA |
| Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2 | 50 kA |
| Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2 | 50 kA |
| Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2 | 25 kA |
| Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2 | 25 kA |
| Rated short circuit breaking capacity Icn under 240V AC according IEC 60898-1 | 10 kA |
| Rated short circuit breaking capacity Icn under 415V AC according IEC 60898-1 | 10 kA |
| Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2 | 50 kA |
| Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2 | 25 kA |
| Current correction factors | |
| Correction factor of rating current for 2 devices placed side-by-side | 1 |
| Correction factor of rating current for 3 devices placed side-by-side | 0.95 |
| Correction factor of rating current for 4 and 5 devices placed side-by-side | 0.9 |
| Correction factor of rating current for 6 devices placed side-by-side | 0.85 |

| | |
|--|-----|
| Correction factor of magnetic tripping with 100 Hz | 1.1 |
| Correction factor of magnetic tripping with 200 Hz | 1.2 |
| Correction factor of magnetic tripping with 400 Hz | 1.5 |
| Correction factor of magnetic tripping with 60 Hz | 1 |

Dimensions

| | |
|-----------------------------|---------|
| Depth of installed product | 70 mm |
| Height of installed product | 83 mm |
| Width of installed product | 52.5 mm |

Frequency

| | |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

Power

| | |
|---|--------|
| Maximum power loss per pole according to the product standard | 4.5 W |
| Total power loss under IN | 11 W |
| Power loss per pole at In | 3.73 W |

Tripping

| | |
|-------------------------------|------|
| Time of response when opening | 7 ms |
|-------------------------------|------|

Endurance

| | |
|--|-------|
| Electric endurance in number of cycles | 4000 |
| Number of mechanical operations | 20000 |

Installation, mounting

| | |
|---|------------|
| Type of top connection for modular devices | with screw |
| Tightening torque | 2,8Nm |
| Type of top rail clip for modular devices | NA |
| Type of bottom rail clip for modular devices | plastic |
| Type of Bottom Connection for modular devices | Blconnect |
| Top removability for modular devices | Yes |
| Bottom removability for modular devices | Yes |
| Suitable for flush-mounting | Yes |

Connection

| | |
|--|------------------------|
| Connection cross-section at output with screw, for flexible conductor | 1 / 25 mm ² |
| Connection cross-section at output with screw, for massive conductor | 1 / 35 mm ² |
| Connection cross-section for rigid conductor, upstream terminals with screws | 1 / 35 mm ² |
| Connection cross-section of the access with screws, with flexible conductor | 1 / 25 mm ² |
| Downstream cage clamp delivery status | opened |
| Upstream cage clamp delivery status | opened |

Equipment

Subject to technical modifications

Can be accessorized

Yes

Standards

| | |
|---------------|-------------|
| Standard text | IEC 60947-2 |
|---------------|-------------|

Safety

| | |
|---------------|----|
| REACH conform | No |
|---------------|----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

| | |
|--------------|----|
| Halogen free | No |
|--------------|----|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -25...70 °C |
|-----------------------|-------------|

| | |
|---|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
|---|---|

| | |
|---|---|
| Class of energy limitation I ² t | 3 |
|---|---|

| | |
|----------|--------|
| Altitude | 2000 m |
|----------|--------|

| | |
|-------------------------|------------------|
| Air humidity protection | for all climates |
|-------------------------|------------------|

| | |
|-------------------------------|-------------|
| Storage/transport temperature | -25...80 °C |
|-------------------------------|-------------|

temperatur

| | |
|----------------------------|-------|
| Temperature of calibration | 50 °C |
|----------------------------|-------|