



NSN363



MCB 3P 15kA D-63A 3M

Technical properties

Architecture

Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Type of pole	3 P
Fixing mode	Din-Rail

Functions

Concurrently switching N-neutral	No
----------------------------------	----

Configuration

Number of modules	3
-------------------	---

Connectivity

Top connection alignment for modular devices	Aligned terminal
Bottom connection alignment for modular devices	Aligned terminal

Main electrical features

Rated operational voltage Ue	415 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V
Minimum threshold voltage (Ue min)	12 V

Electric current

Rated current	63 A
Rated service breaking capacity Ics AC according IEC 60898-1	7.5 kA
min/maxi threshold value of the AC thermal operation	1.13 / 1.45 In
Magnetic regulating current	10 / 14.4 In
min/maxi threshold value of the DC magnetic operation	10 / 30 In
min/maxi threshold value of the DC thermal operation	1.13 / 1.45 In
Breaking capacity on 1 pole for IT 400V NF 60947-2	3 kA

Rated short circuit breaking capacity Icn under 230V AC according IEC60898-1	10 kA
Rated short circuit breaking capacity Icn under 400V AC according IEC60898-1	10 kA
Rated short circuit breaking capacity Icn under 240V AC according IEC 60898-1	10 kA
Rated short circuit breaking capacity Icn under 415V AC according IEC 60898-1	10 kA

Electric current / temperature

Rating current -25°C	78.67 A
Rating current -20°C	77.38 A
Rating current -15°C	76.06 A
Rating current -10°C	74.72 A
Rating current -5°C	73.36 A
Rating current 0°C	71.97 A
Rating current 5°C	70.56 A
Rating current 10°C	69.11 A
Rating current 15°C	67.64 A
Rating current 20°C	66.13 A
Rating current 25°C	64.58 A
Rating current 30°C	63 A
Rating current 35°C	60.96 A
Rating current 40°C	58.86 A
Rating current 45°C	56.68 A
Rating current 50°C	54.4 A
Rating current 55°C	52.03 A
Rating current 60°C	49.55 A
Rating current 65°C	46.94 A
Rating current 70°C	44.17 A

Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.95
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.9
Correction factor of rating current for 6 devices placed side-by-side	0.85
Correction factor of magnetic tripping with 100 Hz	1.1
Correction factor of magnetic tripping with 200 Hz	1.2
Correction factor of magnetic tripping with 400 Hz	1.5
Correction factor of magnetic tripping with 60 Hz	1

Dimensions

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	52.5 mm

Subject to technical modifications

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	19.9 W
Power loss per pole at In	7.12 W

Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

Installation, mounting

Type of top connection for modular devices	with screw
Tightening torque	2,8Nm
Type of top rail clip for modular devices	NA
Type of bottom rail clip for modular devices	plastic
Type of Bottom Connection for modular devices	Blconnect
Top removability for modular devices	Yes
Bottom removability for modular devices	Yes

Connection

Connection cross-section of input and output with screws, for massive conductors	1 / 35 mm ²
Connection cross section of access and exit with screws, for flexible conductor	1 / 25 mm ²

Equipment

With transparent product label holder	Yes
---------------------------------------	-----

Standards

Standard text	IEC 60947-2
European directive WEEE	concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...70 °C
Altitude	2000 m
Storage/transport temperature	-25...80 °C