



NRN332



MCB 3P 20kA C-32A 3M

Technical properties

Architecture

Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Type of pole	3 P
Curve	C

Functions

Concurrently switching N-neutral	No
----------------------------------	----

Configuration

Number of modules	3
-------------------	---

Connectivity

Top connection alignment for modular devices	Aligned terminal
Bottom connection alignment for modular devices	Aligned terminal

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	10 kA
Rated operational voltage U_e	415 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	500 V
Max operating voltage	415 V
Rated impulse withstand voltage	6000 V

Electric current

Rated current	32 A
Rated service breaking capacity I_{cs} AC according IEC 60898-1	7.5 kA
min/maxi threshold value of the AC thermal operation	1.13 / 1.45 I_n
Magnetic regulating current	5 / 10 I_n
min/maxi threshold value of the DC magnetic operation	5 / 15 I_n
min/maxi threshold value of the DC thermal operation	1.13 / 1.45 I_n
Rating current -10°C according to IEC 60947	41.08 A

Rating current -15°C according to IEC 60947	41.74 A
Rating current -20°C according to IEC 60947	42.4 A
Rating current -25°C according to IEC 60947	43.05 A
Rating current -5°C according to IEC 60947	40.4 A
Rating current 0°C according to IEC 60947	39.71 A
Rating current 10°C according to IEC 60947	38.29 A
Rating current 15°C according to IEC 60947	37.56 A
Rating current 20°C according to IEC 60947	36.82 A
Rating current 25°C according to IEC 60947	36.06 A
Rating current 30°C according to IEC 60947	35.29 A
Rating current 35°C according to IEC 60947	34.49 A
Rating current 40°C according to IEC 60947	33.68 A
Rating current 45°C according to IEC 60947	32.85 A
Rating current 5°C according to IEC 60947	39.01 A
Rating current 50°C according to IEC 60947	32 A
Rating current 55°C according to IEC 60947	31.09 A
Rating current 60°C according to IEC 60947	30.16 A
Rating current 65°C according to IEC 60947	29.19 A
Rating current 70°C according to IEC 60947	28.19 A
Breaking capacity on 1 pole for IT 400V NF 60947-2	3 kA
Rated short circuit breaking capacity I _{cn} under 230V AC according IEC60898-1	10 kA
Rated short circuit breaking capacity I _{cn} under 400V AC according IEC60898-1	10 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 230V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 240V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 400V AC IEC 60947-2	20 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 415V AC IEC 60947-2	20 kA
Rated short circuit breaking capacity I _{cn} under 240V AC according IEC 60898-1	10 kA
Rated short circuit breaking capacity I _{cn} under 415V AC according IEC 60898-1	10 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 220V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 380V AC IEC 60947-2	20 kA
Current correction factors	
Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.95
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.9
Correction factor of rating current for 6 devices placed side-by-side	0.85

Correction factor of magnetic tripping with 100 Hz	1.1
Correction factor of magnetic tripping with 200 Hz	1.2
Correction factor of magnetic tripping with 400 Hz	1.5
Correction factor of magnetic tripping with 60 Hz	1

Dimensions

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	52.5 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Maximum power loss per pole according to the product standard	6 W
Total power loss under IN	12.3 W
Power loss per pole at In	4.22 W

Tripping

Time of response when opening	7 ms
-------------------------------	------

Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

Installation, mounting

Type of top connection for modular devices	with screw
Tightening torque	2,8Nm
Type of top rail clip for modular devices	NA
Type of bottom rail clip for modular devices	plastic
Type of Bottom Connection for modular devices	Blconnect
Top removability for modular devices	Yes
Bottom removability for modular devices	Yes
Suitable for flush-mounting	Yes

Connection

Connection cross-section at output with screw, for flexible conductor	1 / 25 mm ²
Connection cross-section at output with screw, for massive conductor	1 / 35 mm ²
Connection cross-section for rigid conductor, upstream terminals with screws	1 / 35 mm ²
Connection cross-section of the access with screws, with flexible conductor	1 / 25 mm ²
Downstream cage clamp delivery status	opened
Upstream cage clamp delivery status	opened

Equipment

Subject to technical modifications

Standards

Standard text	IEC 60947-2
---------------	-------------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-25...70 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I ² t	3
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-25...80 °C

temperatur

Temperature of calibration	50 °C
----------------------------	-------