



SBB225

2-pole, 25A Modular Switch with Indicator Light

Technical properties

Architecture

Type of order	Break switch with light
Neutral position	without neutral
Number of poles	2 P
Type of pole	2 P

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	440 V
Type of voltage input 1	AC
Rated impulse withstand voltage	4000 V

Electric current

Rated operational current in AC21category B	25 A
Acceptable current rating with AC22 category A	25 A
Rated current	25 A
Rated short-time withstand current 1s	0.375 kA
Thermal rated current outside of housings	25 A
Rated operational current in AC21 category A	25 A
Acceptable current rating with AC22 category B	25 A

Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	1.9 W
Power loss per pole at In	0.9 W

Endurance	
Electrical durability at nominal load in AC21 in operating cycles	25000
Electrical durability at nominal load in AC22 in operating cycles	25000
Number of mechanical operations	200000
Lighting control	
Light colour	orange
Type of lamp	LED
Installation, mounting	
Tightening torque	1,8Nm
Connection	
Connection cross-sect. flexible conductor	1,5 / 10mm ²
Connection cross-sect. rigid cable	1,5 / 16mm ²
Lamp socket type	Sans
Cage clamp position	off set
Type of connection	with screw
Equipment	
Quantity of NC contacts	0
Quantity of NO contacts	2
Quantity of INV contacts	0
Standards	
Standard text	IEC 60947-3 ; IEC/EN 60669-1
Safety	
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-20...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Storage/transport temperature	-40...80 °C