



SBN125

## 1-pole, 25A Modular Switch

### Technical properties

#### Architecture

Neutral position	without neutral
Number of poles	1 P
Type of pole	1 P

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	440 V
Type of voltage input 1	AC
Rated impulse withstand voltage	4000 V

#### Electric current

Rated operational current in AC21 category B	25 A
Acceptable current rating with AC22 category A	25 A
Rated current	25 A
Rated short-time withstand current 1s	0.375 kA
Thermal rated current outside of housings	25 A
Rated operational current in AC21 category A	25 A
Acceptable current rating with AC22 category B	25 A

#### Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Total power loss under IN	0.9 W
Power loss per pole at In	0.9 W

**Endurance**

---

Electrical durability at nominal load in AC21 in operating cycles	25000
Electrical durability at nominal load in AC22 in operating cycles	25000
Number of mechanical operations	200000

**Connection**

---

Cage clamp position	off set
---------------------	---------

**Equipment**

---

Quantity of NC contacts	0
Quantity of NO contacts	1
Quantity of INV contacts	0

**Standards**

---

Standard text	IEC 60947-3 ; IEC/EN 60669-2 ; IEC/EN 60669-4
European directive WEEE	concerned

**Safety**

---

Protection index IP	IP20
---------------------	------

**Use conditions**

---

Operating temperature	-20...50 °C
Altitude	2000 m
Storage/transport temperature	-40...80 °C