



SA463



## Trip free switch 4P 63A

### Technical properties

#### Architecture

Number of poles	4 P
Type of pole	4 P

#### Configuration

Number of modules	4.5
-------------------	-----

#### Main electrical features

Rated operational voltage Ue	230 / 415 V
------------------------------	-------------

#### Voltage

Type of voltage input 1	AC
-------------------------	----

#### Electric current

Rated current	63 A
Rated short-time withstand current 1s	800 A

#### Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	79 mm

#### Power

Total power loss under I <sub>N</sub>	14.09 W
Power loss per pole at I <sub>n</sub>	3.69 W

#### Equipment

Quantity of NC contacts	1
Quantity of NO contacts	5
Quantity of INV contacts	0

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-25...40 °C
Storage/transport temperature	-25...70 °C