



SBN190

1-pole, 100A Modular Switch

Technical properties

Architecture

Neutral position	without neutral
Number of poles	1 P
Type of pole	1 P

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	440 V
Type of voltage input 1	AC
Rated impulse withstand voltage	6000 V

Electric current

Rated operational current in AC21category B	100 A
Acceptable current rating with AC22 category A	100 A
Rated current	100 A
Rated short-time withstand current 1s	1.2 kA
Thermal rated current outside of housings	100 A
Rated operational current in AC21 category A	100 A
Acceptable current rating with AC22 category B	100 A

Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	5.5 W
Power loss per pole at In	5.5 W

Endurance

Electrical durability at nominal load in AC21 in operating cycles	2500
Electrical durability at nominal load in AC22 in operating cycles	2500
Number of mechanical operations	40000

Connection

Cage clamp position	in line
---------------------	---------

Equipment

Quantity of NC contacts	0
Quantity of NO contacts	1
Quantity of INV contacts	0

Standards

Standard text	IEC 60947-3
European directive WEEE	not concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...50 °C
Altitude	2000 m
Storage/transport temperature	-40...80 °C