



SBN233

**2-pole, 32A Modular Switch with big terminals**

**Technical properties**

**Architecture**

Type of order	Break switch
Neutral position	without neutral
Number of poles	2 P
Type of pole	2 P

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	440 V
Type of voltage input 1	AC
Rated impulse withstand voltage	6000 V

**Electric current**

Rated current	32 A
Thermal rated current outside of housings	32 A

**Dimensions**

Depth of installed product	68 mm
----------------------------	-------

**Frequency**

Frequency	50 to 60 Hz
-----------	-------------

**Power**

Total power loss under I <sub>N</sub>	2.3 W
Power loss per pole at I <sub>n</sub>	1.2 W

**Connection**

Type of connection	with screw
--------------------	------------

**Equipment**

Quantity of NC contacts	0
Quantity of NO contacts	2
Quantity of INV contacts	0

**Standards**

**Use conditions**

---

Operating temperature	-20...50 °C
Storage/transport temperature	-40...80 °C

---