



SBN425

4-pole, 25A Modular Switch

Technical properties

Architecture

Neutral position	without neutral
Number of poles	4 P
Type of pole	4 P

Configuration

Number of modules	2
-------------------	---

Main electrical features

Rated operational voltage Ue	400 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	440 V
Type of voltage input 1	AC
Rated impulse withstand voltage	4000 V

Electric current

Rated operational current in AC21category B	25 A
Acceptable current rating with AC22 category A	25 A
Rated current	25 A
Rated short-time withstand current 1s	0.375 kA
Thermal rated current outside of housings	25 A
Rated operational current in AC21 category A	25 A
Acceptable current rating with AC22 category B	25 A

Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	35 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	3.6 W
Power loss per pole at In	0.9 W

Endurance

Electrical durability at nominal load in AC21in operating cycles	25000
Electrical durability at nominal load in AC22 in operating cycles	25000
Number of mechanical operations	200000

Connection

Cage clamp position	off set
---------------------	---------

Equipment

Quantity of NC contacts	0
Quantity of NO contacts	4
Quantity of INV contacts	0

Standards

Standard text	IEC 60947-3 ; IEC/EN 60669-2 ; IEC/EN 60669-4
European directive WEEE	not concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...50 °C
Altitude	2000 m
Storage/transport temperature	-40...80 °C