



SF218F



## Technical properties

### Architecture

Number of poles 2 P

### Configuration

Number of modules 2

### Main electrical features

Rated operational voltage  $U_e$  250 V

### Electric current

Rated current 25 A

### Dimensions

Depth of installed product 67.5 mm

Height of installed product 81 mm

Width of installed product 35 mm

### Power

Total power loss under  $I_N$  1.8 W

### Endurance

Number of mechanical operations 150000

### Installation, mounting

Tightening torque 2,9Nm

### Connection

Connection cross-sect. flexible conductor 10mm<sup>2</sup>

Connection cross-sect. rigid cable 16mm<sup>2</sup>

Number of contacts 2

Type of contacts 1 changeover