



SF463

4 pole Changeoverswitch 63A I-0-II

Technical properties

Architecture

Number of poles	4 P
-----------------	-----

Configuration

Number of modules	8
-------------------	---

Main electrical features

Rated operational voltage Ue	400 V
------------------------------	-------

Frequency	50/60 Hz
-----------	----------

Voltage

Rated insulation voltage	500 V
--------------------------	-------

Rated impulse withstand voltage	4000 V
---------------------------------	--------

Electric current

Rated current	63 A
---------------	------

Short circuit current withstand with MCB 63A Curve C - 4,5kA	4.5 kA
---	--------

Rated operational current in AC21	63 A
-----------------------------------	------

Dimensions

Depth of installed product	72 mm
----------------------------	-------

Height of installed product	90 mm
-----------------------------	-------

Width of installed product	143 mm
----------------------------	--------

Power

Total power loss under IN	7.2 W
---------------------------	-------

Endurance

Electrical durability at nominal load in AC21in operating cycles	5000
---	------

Number of mechanical operations	100000
---------------------------------	--------

Installation, mounting

Tightening torque	2,9Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	16mm ²
---	-------------------

Connection cross-sect. rigid cable	25mm ²
------------------------------------	-------------------

Type of contacts	changeover with zero position
------------------	-------------------------------

Type of connection	with screw
--------------------	------------

Standards

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Operating temperature -20...50 °C

Storage/transport temperature -40...80 °C