



SPA001N

**Cartridge N-PE Uc 350V Iimp 100kA Up 1.5kV**

**Technical properties**

**Configuration**

Number of modules	2
-------------------	---

**Main electrical features**

Test class type1 IEC61643-11	Yes
Frequency	50/60 Hz
Nominal discharge current (In) 8/20μs, IEC 61643)L-N(PEN)/ N-PE	100 kA

**Electric current**

Calibration of the protection upstream	315 A
Max discharge (Imax) L-N(PEN)/ N-PE	100 kA

**Dimensions**

Depth of installed product	52.3 mm
Height of installed product	46.4 mm
Width of installed product	35.5 mm

**Standards**

Test class IEC61643-11 / VDE0675-6-11	T1 ; T2
European directive WEEE	concerned

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-40...80 °C
Storage/transport temperature	-40...80 °C