



SPA001N

Cartridge N-PE Uc 350V Iimp 100kA Up 1.5kV

Technical properties

Configuration

Number of modules	2
-------------------	---

Controls and indicators

Indicator lamp	Optic
----------------	-------

Main electrical features

Test class type1 IEC61643-11	Yes
Nominal discharge current (In) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE	100 kA

Electric current

Calibration of the protection upstream	315 A
Max discharge (Imax) L-N(PEN)/ N-PE	100 kA

Dimensions

Depth of installed product	52.3 mm
Height of installed product	46.4 mm
Width of installed product	35.5 mm

Standards

Test class IEC61643-11 / VDE0675-6-11	T1 ; T2
European directive WEEE	concerned

Use conditions

Operating temperature	-40...80 °C
Storage/transport temperature	-40...80 °C