



SPA800

Combined SPD T1+T2 3P Uc 350V Iimp 25kA In 25kA Up 1.5kV TCN with remote contact

Technical properties

Configuration

Number of modules 6

Main electrical features

Test class type1 IEC61643-11 Yes

Frequency 50/60 Hz

Nominal discharge current (In) 8/20µs, IEC 61643)L-N(PEN)/ N-PE 25 / 75 kA

Electric current

Calibration of the protection upstream 315 A

Max discharge (Imax) L-N(PEN)/ N-PE 50 kA

Dimensions

Depth of installed product 67 mm

Height of installed product 95.2 mm

Width of installed product 106.8 mm

Electrical specifications

Signal contact Cross-sections 0.14 / 1.5 mm²

Signal contact Current carrying capacity AC/DC 1 / 0.2 A

Signal contact Voltage rating AC/DC 250 / 125 V

Network configuration

Network type TN-C

Installation, mounting

Tightening torque 4,5Nm

Standards

Test class IEC61643-11 / VDE0675-6-11 T1 ; T2

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Operating temperature -40...80 °C

Storage/transport temperature -40...80 °C