



SPA800

**Combined SPD T1+T2 3P Uc 350V Iimp 25kA In 25kA Up 1.5kV TCN with remote contact**

**Technical properties**

**Configuration**

Number of modules	6
-------------------	---

**Controls and indicators**

Indicator lamp	Optic
----------------	-------

**Main electrical features**

Test class type1 IEC61643-11	Yes
Frequency	50/60 Hz
Nominal discharge current (In) 8/20 $\mu$ s, IEC 61643)L-N(PEN)/ N-PE	25 / 75 kA

**Electric current**

Calibration of the protection upstream	315 A
Max discharge (Imax) L-N(PEN)/ N-PE	50 kA

**Dimensions**

Depth of installed product	67 mm
Height of installed product	95.2 mm
Width of installed product	106.8 mm

**Electrical specifications**

Signal contact Cross-sections	0.14 / 1.5 mm <sup>2</sup>
Signal contact Current carrying capacity AC/DC	1 / 0.2 A
Signal contact Voltage rating AC/DC	250 / 125 V

**Network configuration**

Network type	TN-C
--------------	------

**Installation, mounting**

Tightening torque	4,5Nm
-------------------	-------

**Standards**

Approvals	CE, VDE, KEMA
Test class IEC61643-11 / VDE0675-6-11	T1 ; T2

**Safety**

REACH conform	No
RoHS conform	Yes
Halogen free	No

**Use conditions**

---

Operating temperature	-40...80 °C
Storage/transport temperature	-40...80 °C

---