



SPB265R

## Surge Protection Device 2P T2 TNS/TT U<sub>c</sub> 320V I<sub>n</sub> 20kA I<sub>max</sub> 65kA remote contact

### Technical properties

#### Configuration

Number of modules	2
-------------------	---

#### Controls and indicators

Indicator lamp	Optic
----------------	-------

#### Main electrical features

Rated operational voltage U <sub>e</sub>	240 / 415 V
Frequency	50/60 Hz
Nominal discharge current (I <sub>n</sub> ) 8/20μs, IEC 61643)L-N(PEN)/ N-PE	20 kA

#### Voltage

Maximum continuous operating voltage U <sub>c</sub>	320 V
Voltage protection level U <sub>p</sub> according to IEC61643-1	1.45 kV
Voltage protection level U <sub>p</sub> L-PE/N-PE according to IEC61643-11	1.7 kV
Voltage level U <sub>p</sub> L-N/PEN IEC61643-11	1.45 kV

#### Electric current

Calibration of the protection upstream	160 A
Max discharge (I <sub>max</sub> ) L-N(PEN)/ N-PE	65 kA

#### Dimensions

Depth of installed product	58.2 mm
Height of installed product	89.8 mm
Width of installed product	35.6 mm

#### Electrical specifications

Short-circuit breaking capacity (I <sub>sc</sub> cr)	25 kA
Signal contact Cross-sections	0.14 / 1.5 mm <sup>2</sup>
Signal contact Current carrying capacity AC/DC	3 / 1 A
Signal contact Voltage rating AC/DC	250 / 30 V

#### Network configuration

Network type	TT/TN-S
--------------	---------

#### Installation, mounting

Tightening torque	3
-------------------	---

#### Connection

Connection cross-section of input and output with screws, for massive conductors	1.5 / 35 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	1.5 / 25 mm <sup>2</sup>
<b>Standards</b>	
Approvals	KEMA, NF
Test class IEC61643-11 / VDE0675-6-11	T2
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
<b>Use conditions</b>	
Operating temperature	-40...80 °C