



SF263



2 pole Changeoverswitch 63A I-0-II

Technical properties

Architecture

Number of poles 2 P

Configuration

Number of modules 4

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50/60 Hz

Voltage

Rated insulation voltage 500 V

Rated impulse withstand voltage 4000 V

Electric current

Rated current 63 A

Short circuit current withstand with MCB
63A Curve C - 4,5kA 4.5 kA

Rated operational current in AC21 63 A

Dimensions

Depth of installed product 72 mm

Height of installed product 90 mm

Width of installed product 71.5 mm

Power

Total power loss under IN 3.6 W

Endurance

Electrical durability at nominal load in
AC21in operating cycles 5000

Number of mechanical operations 100000

Installation, mounting

Tightening torque 2,9Nm

Connection

Type of connection with screw

Standards

European directive WEEE concerned

Safety

| | |
|-------------------------------|-------------|
| Protection index IP | IP20 |
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |
| Use conditions | |
| Operating temperature | -20...50 °C |
| Storage/transport temperature | -40...80 °C |