



SPA001N

Cartridge N-PE Uc 350V Iimp 100kA Up 1.5kV

Technical properties

Configuration

Number of modules	2
-------------------	---

Controls and indicators

Indicator lamp	Optic
----------------	-------

Main electrical features

Test class type1 IEC61643-11	Yes
------------------------------	-----

Frequency	50/60 Hz
-----------	----------

Nominal discharge current (In) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE	100 kA
---	--------

Electric current

Calibration of the protection upstream	315 A
--	-------

Max discharge (Imax) L-N(PEN)/ N-PE	100 kA
-------------------------------------	--------

Dimensions

Depth of installed product	52.3 mm
----------------------------	---------

Height of installed product	46.4 mm
-----------------------------	---------

Width of installed product	35.5 mm
----------------------------	---------

Standards

Approvals	CE, VDE, KEMA
-----------	---------------

Test class IEC61643-11 / VDE0675-6-11	T1 ; T2
---------------------------------------	---------

Use conditions

Operating temperature	-40...80 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------