



SPK602

Surge protection for ADSL DIN-Rail

Technical properties

Configuration

Earthing via Separate conductor

Controls and indicators

Indicator lamp no

Main electrical features

Rated operational voltage U_e 130 V

Nominal voltage 130 V

Voltage

Maximum continuous operating voltage U_c 185 V

Rated operational voltage in DC 185 V

Voltage protection level U_p according to IEC61643-1 300 V

Maximum continuous operating voltage U_c DC IEC61643 185 V

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE 10 kA

Dimensions

Depth of installed product 58 mm

Height of installed product 90 mm

Width of installed product 17.7 mm

Width 17.7 mm

Frequency

Frequency 50 to 60 Hz

Installation, mounting

Tightening torque 0.5Nm

Mounting type din-Rail

Connection

Type of connection with screw

Standards

Approvals CE, KEMA

Test class IEC61643-11 / VDE0675-6-11 B2 ; C1 ; C2 ; C3 ; D1

European directive WEEE concerned

Use conditions

Operating temperature	-40...85 °C
Storage/transport temperature	-40...85 °C
