



SPA081

Cartridge L-N/PEN Uc 350V Iimp 25kA Up 1.5kV for SPA80X

Technical properties

Configuration

Number of modules	2
-------------------	---

Main electrical features

Test class type1 IEC61643-11	Yes
Frequency	50/60 Hz
Nominal discharge current (In) 8/20μs, IEC 61643)L-N(PEN)/ N-PE	25 kA

Electric current

Calibration of the protection upstream	315 A
Max discharge (Imax) L-N(PEN)/ N-PE	50 kA

Dimensions

Depth of installed product	52.3 mm
Height of installed product	46.4 mm
Width of installed product	35.5 mm

Standards

Test class IEC61643-11 / VDE0675-6-11	T1 ; T2
European directive WEEE	concerned

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-40...80 °C
Storage/transport temperature	-40...80 °C