



SPA801

Combined SPD T1+T2 4P Uc 350V Iimp 25kA Up 1.5kV TNS/TT with remote contact

Technical properties

Configuration

Number of modules 8

Controls and indicators

Indicator lamp Optic

Main electrical features

Test class type1 IEC61643-11 Yes

Frequency 50/60 Hz

Nominal discharge current (In) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE 25 / 100 kA

Electric current

Calibration of the protection upstream 315 A

Max discharge (I_{max}) L-N(PEN)/ N-PE 50 kA

Dimensions

Depth of installed product 67 mm

Height of installed product 95.2 mm

Width of installed product 142.4 mm

Electrical specifications

Signal contact Cross-sections 0.14 / 1.5 mm²

Signal contact Current carrying capacity AC/DC 1 / 0.2 A

Signal contact Voltage rating AC/DC 250 / 125 V

Network configuration

Network type TT/TN-S

Installation, mounting

Tightening torque 4,5Nm

Standards

Approvals CE, VDE, KEMA

Test class IEC61643-11 / VDE0675-6-11 T1 ; T2

Safety

Halogen free No

Use conditions

Operating temperature -40...80 °C

