



SPN065N

## Cartridge neutral 65kA 255V for pluggable SPD with reserve

### Technical properties

#### Architecture

Number of poles 1 P

#### Configuration

Number of modules 1

#### Connectivity

Top connection alignment for modular devices Not applicable

#### Main electrical features

Frequency 50/60 Hz

Nominal discharge current (In) 8/20 $\mu$ s, IEC 61643)L-N(PEN)/ N-PE 40 kA

#### Voltage

Maximum continuous operating voltage Uc 255 V

Voltage protection level Up according to IEC61643-1 1.5 kV

#### Electric current

Max discharge (Imax) L-N(PEN)/ N-PE 65 kA

#### Dimensions

Width of installed product 0 mm

#### Power

Total power loss under IN 0 W

#### Standards

Test class IEC61643-11 / VDE0675-6-11 T2

European directive WEEE concerned

#### Use conditions

Operating temperature -40...55 °C

Storage/transport temperature -40...80 °C