



SPN065R

Cartridge 65kA 275V for pluggable SPD with reserve

Technical properties

Architecture

Number of poles 1 P

Configuration

Number of modules 1

Connectivity

Top connection alignment for modular devices Not applicable

Main electrical features

Frequency 50/60 Hz

Nominal discharge current (In) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE 20 kA

Voltage

Maximum continuous operating voltage Uc 275 V

Voltage protection level Up according to IEC61643-1 1.5 kV

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE 65 kA

Dimensions

Width of installed product 0 mm

Power

Total power loss under IN 0 W

Standards

Test class IEC61643-11 / VDE0675-6-11 T2

European directive WEEE concerned

Use conditions

Operating temperature -40...55 °C

Altitude 2000 m

Storage/transport temperature -40...80 °C