



SPA801

**Combined SPD T1+T2 4P Uc 350V Iimp 25kA Up 1.5kV TNS/TT with remote contact**

**Technical properties**

**Configuration**

Number of modules 8

**Controls and indicators**

Indicator lamp Optic

**Main electrical features**

Test class type1 IEC61643-11 Yes

Frequency 50/60 Hz

Nominal discharge current (In) 8/20 $\mu$ s, IEC 61643)L-N(PEN)/ N-PE 25 / 100 kA

**Electric current**

Calibration of the protection upstream 315 A

Max discharge (I<sub>max</sub>) L-N(PEN)/ N-PE 50 kA

**Dimensions**

Depth of installed product 67 mm

Height of installed product 95.2 mm

Width of installed product 142.4 mm

**Electrical specifications**

Signal contact Cross-sections 0.14 / 1.5 mm<sup>2</sup>

Signal contact Current carrying capacity AC/DC 1 / 0.2 A

Signal contact Voltage rating AC/DC 250 / 125 V

**Network configuration**

Network type TT/TN-S

**Installation, mounting**

Tightening torque 4,5Nm

**Standards**

Approvals CE, VDE, KEMA

Test class IEC61643-11 / VDE0675-6-11 T1 ; T2

**Safety**

Halogen free No

**Use conditions**

Operating temperature -40...80 °C

