



SPN240D

## SPD 2P pluggable 40kA class 2 with end of life indicator

### Technical properties

#### Architecture

Type of pole	1P+N
--------------	------

#### Configuration

Number of modules	2
-------------------	---

#### Controls and indicators

Indicator lamp	end of life indicator
----------------	-----------------------

#### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Nominal discharge current (In) 8/20μs, IEC 61643)L-N(PEN)/ N-PE	15 kA

#### Voltage

Maximum continuous operating voltage Uc	275 V
Voltage protection level Up according to IEC61643-1	1.2 kV

#### Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	40 kA
-------------------------------------	-------

#### Dimensions

Width of installed product	36 mm
----------------------------	-------

#### Power

Total power loss under IN	0 W
---------------------------	-----

#### Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	25mm <sup>2</sup>
Connection cross-sect. rigid cable	35mm <sup>2</sup>

#### Standards

Test class IEC61643-11 / VDE0675-6-11	T2
---------------------------------------	----

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Operating temperature	-40...55 °C
Storage/transport temperature	-40...80 °C