



SPN465R

SPD 4P pluggable 65kA class 2 with reserve + remote contact

Technical properties

Configuration

Number of modules 4

Controls and indicators

Indicator lamp reserve

Main electrical features

Rated operational voltage U_e 230 / 400 V

Nominal discharge current (I_n) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE 20 kA

Voltage

Maximum continuous operating voltage U_c 275 V

Voltage protection level U_p according to IEC61643-1 1.5 kV

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE 65 kA

Dimensions

Width of installed product 72 mm

Power

Total power loss under I_N 0 W

Installation, mounting

Tightening torque 3,6Nm

Connection

Connection cross-sect. flexible conductor 25mm²

Connection cross-sect. rigid cable 35mm²

Standards

Test class IEC61643-11 / VDE0675-6-11 T2

European directive WEEE concerned

Use conditions

Operating temperature -40...55 °C

Storage/transport temperature -40...80 °C