



SPN465R

## SPD 4P pluggable 65kA class 2 with reserve + remote contact

### Technical properties

#### Configuration

Number of modules	4
-------------------	---

#### Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50/60 Hz
Nominal discharge current (In) 8/20 $\mu$ s, IEC 61643)L-N(PEN)/ N-PE	20 kA

#### Voltage

Maximum continuous operating voltage Uc	275 V
Voltage protection level Up according to IEC61643-1	1.5 kV

#### Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	65 kA
-------------------------------------	-------

#### Dimensions

Width of installed product	72 mm
----------------------------	-------

#### Power

Total power loss under IN	0 W
---------------------------	-----

#### Standards

Test class IEC61643-11 / VDE0675-6-11	T2
European directive WEEE	concerned

#### Use conditions

Operating temperature	-40...55 °C
Storage/transport temperature	-40...80 °C