



SPN715D

SPD 2P auto-protected pluggable 15kA class 2 with end of life indicator

Technical properties

Architecture

Type of pole 1P+N

Configuration

Number of modules 2

Controls and indicators

Indicator lamp end of life indicator

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50/60 Hz

Nominal discharge current (I_n) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE 5 kA

Voltage

Maximum continuous operating voltage U_c 275 V

Voltage protection level U_p according to IEC61643-1 1.5 kV

Electric current

Max discharge (I_{max}) L-N(PEN)/ N-PE 15 kA

Dimensions

Depth of installed product 70 mm

Width of installed product 36 mm

Power

Total power loss under I_N 0 W

Installation, mounting

Tightening torque 3,6Nm

Connection

Connection cross-sect. flexible conductor 16mm²

Connection cross-sect. rigid cable 10mm²

Standards

Test class IEC61643-11 / VDE0675-6-11 T2

Use conditions

Operating temperature -40...55 °C

Storage/transport temperature -40...80 °C

